

TECHSPEC® 25mm Dia. x 30mm FL, Uncoated, Hybrid Asphere



TECHSPEC® Plastic Hybrid Aspheric Lenses

Stock **#21-226** 3-4 DAYS

[Other Coating Options](#)

⊖ 1 ⊕ **€84,00**

ADD TO CART

Qty 1-24

€84,00

Qty 25+

€64,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
25.00 ±0.15

Effective Focal Length EFL (mm):
30.00 @ 587.6nm

Numerical Aperture NA:
0.42

Back Focal Length BFL (mm): 25.82
Substrate:  Zeonex K22R
Aspheric Design Wavelength (nm): 587.6
Coating: Uncoated
Surface Quality: 80-50
Clear Aperture CA (mm): 23.00
Edge Thickness ET (mm): 3.6
Center Thickness CT (mm): 7.30 ±0.20
f#: 1.2
Bevel: Protective bevel as needed
Operating Temperature (°C): -30 to +70
Radius R₂ (mm): 127
Shape of Back Surface: Convex
Type: Aspheric Lens
Wavelength Range (nm): 475 - 675
Conjugate Distance: Infinite

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View