


In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Best Form Spherical Lenses



Stock #22-569 3-4 DAYS



1



€199,00

ADD TO CART

Qty 1-9

€199,00

Qty 10+

€179,10

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
25.00 +0/-0.025

Back Focal Length BFL (mm):
35.06

Effective Focal Length EFL (mm): 40.00
Coating: Uncoated
Substrate:  Fused Silica
Surface Quality: 10-5
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Centering (arcmin): <1
Bevel: Protective bevel as needed
Center Thickness CT (mm): 9.00 ±0.05
Edge Thickness ET (mm): 4.31
Radius R₁ (mm): 80.56
Radius R₂ (mm): 22.91
Clear Aperture CA (mm): 22.50
f/#: 1.6
Focal Length Specification Wavelength (nm): 587.6
Numerical Aperture NA: 0.31
Type: Double-Convex Lens
Wavelength Range (nm): 200 - 2200
Conjugate Distance: Infinite

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View