

25mm Dia. x 50mm FL Protected Gold, Concave Mirror



Stock #43-836 3-4 DAYS

⊖ 1 ⊕ **€58,00**

ADD TO CART

Qty 1-49
€58,00
Qty 50+
€49,50
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Substrate: [N-BK7](#)

Focal Length Tolerance (%):
±2

Surface Quality:
80-50

Diameter (mm):

25.00 ±0.50
Effective Focal Length EFL (mm): 50.00
Radius of Curvature (mm): 100.00
Aperture (f/#): f/2
Coating: Protected Gold (700-10000nm)
Coating Specification: R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm
Coating Type: Metal
Clear Aperture (%): 90
Edge Thickness ET (mm): 3.0
Radius R₁ (mm): 100.00
Thickness Tolerance (mm): ±0.5
Type: Spherical Mirror
Wavelength Range (nm): 700 - 10000

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant
