

TECHSPEC®

25mm Dia. x 50mm FL VIS-NIR Coated Calcium Fluoride PCX Lens



TECHSPEC Calcium Fluoride Plano-Convex (PCX) Lenses

Stock #22-519 3-4 DAYS

-

1

+

€222,50

ADD TO CART

Qty 1-5

€222,50

Qty 6+

€178,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00 +0.00/-0.10

Effective Focal Length EFL (mm):
50.00 @ 266nm

Back Focal Length BFL (mm):

46.58
Coating: VIS-NIR (400-1000nm)
Substrate: ☐ Calcium Fluoride (CaF ₂)
Surface Quality: 40-20
Power (P-V) @ 632.8nm: λ
Irregularity (P-V) @ 632.8nm: λ/2
Centering (arcmin): <3
Center Thickness CT (mm): 5.00 ±0.1
Edge Thickness ET (mm): 1.33
Radius R₁ (mm): 23.11
Clear Aperture CA (mm): 24
f#: 2.00
Numerical Aperture NA: 0.25
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 200 - 7000
Axis Orientation: Random

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant