

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 25mm Dia. X -100mm FL, Uncoated, Double-Concave Lens



Stock #32-994 3-4 DAYS

[Other Coating Options](#)

1 €32,50

ADD TO CART

Qty 1-9

€32,50

Qty 10+

€29,25

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.025

Effective Focal Length EFL (mm):

-100.00
Substrate: N-BK7
f#: 4.00
Numerical Aperture NA: 0.13
Coating: Uncoated
Type: Double-Concave Lens
Wavelength Range (nm): 350 - 2200
Back Focal Length BFL (mm): -101.64
Bevel: Protective bevel as needed
Center Thickness CT (mm): 5.00
Center Thickness Tolerance (mm): ±0.10
Centering (arcmin): <1
Clear Aperture CA (mm): 24.00
Edge Thickness ET (mm): 6.43
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Radius R₁=R₂ (mm): -104.20
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4

Regulatory Compliance

RoHS: Compliant
REACH 201: Compliant
Certificate of Conformance: View