

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union



SUBMIT

25mm Dia X -25.8mm FL Enhanced Aluminum Coated, Convex Mirror



Stock #64-062 [CONTACT US](#)



1



€45,50

ADD TO CART

Qty 1-5

€45,50

Qty 6+

€41,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
25.00 +0.00/-0.10

Focal Length FL (mm):
-25.80

Center Thickness CT (mm):
4.30

Clear Aperture (%):

Coating: Enhanced Aluminum (450-650nm)
Coating Specification: R _{avg} >95% @ 450 - 650nm
Coating Type: Metal
Edge Thickness ET (mm): 2.77
Focal Length Tolerance (%): ±2
Radius R (mm): 51.68
Substrate: ☐ N-BK7
Surface Quality: 60-40
Type: Spherical Mirror
Wavelength Range (nm): 450 - 650
Damage Threshold, Reference: ☐ 0.2 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant
