

TECHSPEC®

25mm Dia x -25mm FL, Protected Aluminum, Convex Mirror



Convex Mirrors

Stock #87-656 3-4 DAYS



1



€47,50

ADD TO CART

Qty 1-5

€47,50

Qty 6+

€38,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00

Focal Length FL (mm):
-25.00

Center Thickness CT (mm):
3.00

Clear Aperture (%) : 90.00
Coating : Protected Aluminum (400-700nm)
Coating Specification : R _{avg} >85% @ 400 - 700nm
Coating Type : Metal
Dimensional Tolerance (mm) : +0.0/-0.1
Edge Thickness ET (mm) : 1.41
Focal Length Tolerance (%) : ±2
Radius R (mm) : 50.0
Substrate : ☐ N-BK7
Surface Accuracy : λ/2
Surface Quality : 60-40
Thickness Tolerance (mm) : ±0.1
Type : Spherical Mirror
Wavelength Range (nm) : 400 - 700

Regulatory Compliance

RoHS 2015 : Compliant
Certificate of Conformance : View
Reach 235 : Compliant