

TECHSPEC® 25mm Dia x -50mm FL, Protected Gold, Convex Mirror



Convex Mirrors

Stock **#87-690** 3-4 DAYS

⊖ 1 ⊕ **€62,00**

ADD TO CART

Qty 1-5
€62,00

Qty 6+
€49,50

Volume Pricing
Request Quote

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00

Focal Length FL (mm):
-50.00

Center Thickness CT (mm):
3.00

Clear Aperture (%) : 90.00
Coating : Protected Gold (700-10000nm)
Coating Specification : R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm
Coating Type : Metal
Dimensional Tolerance (mm) : +0.0/-0.1
Edge Thickness ET (mm) : 2.22
Focal Length Tolerance (%) : ±2
Radius R (mm) : 100.0
Substrate : ☐ N-BK7
Surface Accuracy : λ/2
Surface Quality : 60-40
Thickness Tolerance (mm) : ±0.1
Type : Spherical Mirror
Wavelength Range (nm) : 700 - 2000

Regulatory Compliance

RoHS 2015 : Compliant
Certificate of Conformance : View
Reach 235 : Compliant