

TECHSPEC® 25mm Diameter x -100 FL, VIS 0°, Inked, Plano-Concave Lens



Stock **#47-913-INK** 3-5 DAYS
[Other Coating Options](#)

- 1 + **€54,50**

ADD TO CART

Qty 1-9
€54,50
Qty 10+
€49,00
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00 ±0.025

Effective Focal Length EFL (mm):

-100.00
Substrate: ☐ N-BK7
f#: 4.00
Numerical Aperture NA: 0.13
Coating: VIS 0° (425-675nm)
Type: Plano-Concave Lens
Wavelength Range (nm): 425 - 675
Back Focal Length BFL (mm): -102.31
Bevel: Protective bevel as needed
Center Thickness CT (mm): 3.50
Center Thickness Tolerance (mm): ±0.10
Centering (arcmin): <1
Clear Aperture CA (mm): 24.00
Coating Specification: Ravg ≤0.4% @ 425 - 675nm
Edge Thickness ET (mm): 4.85
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Radius R₁ (mm): -51.68
Surface Quality: 40-20
Damage Threshold, By Design: ☐ 5 J/cm² @ 532nm, 10ns
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View