

[See all 5 Products in Family](#)

25mm Fixed Focal Length Lens



#86-210



Stock **#86-208** [CONTACT US](#)

⊖ 1 ⊕ €1.787⁰⁰

ADD TO CART

Volume Pricing

| | |
|------------|-------------------------------|
| Qty 1+ | €1.787,00 each |
| Need More? | Request Quote |

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Product Family:
4/3" Format Fixed Focal Length Lenses

Type:
Fixed Focal Length Lens

Physical & Mechanical Properties

Iris Option:

| | |
|----------|------------------------|
| Variable | |
| 89.00 | Length (mm): |
| 45.0 | Maximum Diameter (mm): |
| 45 | Outer Diameter (mm): |
| 250.00 | Weight (g): |

Optical Properties

| | |
|------------|---|
| 40.9 | Horizontal Field of View @ Max Sensor Format: |
| 125.00 | Field of View @ Min Working Distance (mm): |
| 21.60 | Maximum Image Circle (mm): |
| 25.00 | Focal Length FL (mm): |
| 150 - ∞ | Working Distance (mm): |
| f/2 - f/16 | Aperture (f/#): |
| <-0.6 | Distortion (%): |
| -0.57 | Maximum Distortion (%): |
| VIS | Lens Wavelength Range: |

Sensor

| | |
|------|------------------------|
| 4/3" | Maximum Sensor Format: |
| 5.00 | Pixel Size (µm): |

Threading & Mounting

| | |
|--------------|----------------|
| M40.5 x 0.50 | Filter Thread: |
| C-Mount | Mount: |

Regulatory Compliance

| | |
|----------------------------------|-----------------------------|
| Exempt | RoHS 2015: |
| View | Certificate of Conformance: |
| Contains SVHC(s) | REACH 241: |

Product Details

- Up to 1", C-Mount Lens
- Less than 1.0% TV Distortion
- 12mm to 50mm Focal Length

Available in multiple focal lengths, 4/3" Format Fixed Focal Length Lenses incorporate a floating focus with aspheric lenses to maximize resolution across their entire working distance. Ideal for many machine vision applications, these fixed focal length lenses feature a broadband anti-reflection (AR) coating for maximum transmission. 4/3" Format Fixed Focal Length Lenses are available with focal lengths ranging from 12 - 50mm.