

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

TECHSPEC

25mm H x 50mm L x -150mm FL MgF₂ Coated,Illumination Grade PCV Cylinder Lens



TECHSPEC® Illumination Grade PCV Cylinder Lenses

Stock #68-085 3-4 DAYS



1



€117,00

ADD TO CART

Qty 1-5

€117,00

Qty 6+

€93,50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Effective Focal Length EFL (mm):
-150.00

Substrate: N-BK7

Coating:

MgF ₂ (400-700nm)
Type: Cylinder Lens, Plano-Concave
Wavelength Range (nm): 400 - 700
Back Focal Length BFL (mm): -152.64
Center Thickness CT (mm): 4.00
Center Thickness Tolerance (mm): ±0.1
Coating Specification: R _{avg} ≤1.75% @400 - 700nm
Dimensional Tolerance (mm): +0.0/-0.2
Dimensions (mm): 25.0 x 50.0
Edge Thickness ET (mm): 4.97
Focal Length Tolerance (%): ±3
Radius R₁ (mm): -77.52
Surface Quality: 60-40
Damage Threshold, By Design: ☐ 10 J/cm ² @532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant