

TECHSPEC®

25mm ID Side Access Mounting Plate, 60° Cutout



#85-640

Stock **#85-640** [CONTACT US](#)

-

1

+

€59⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€59,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Black Anodized Aluminum	Note:
Fixed	Function:

Physical & Mechanical Properties

50 Dia.	Dimensions (mm):
	Thickness (mm):

10.00	
	Plate Inner Diameter (mm):
25.0	
	Bolt Circle Diameter for 6mm Dia. Thru (mm):
38.0	
	Bolt Circle Diameter for M3 C'bore (mm):
38.0	

Threading & Mounting

	Mounting Threads:
C'Bore Holes: (8) M3 Rod Thru Holes: (4) 6 60° cutout for side access	

Regulatory Compliance

	RoHS 2015:
Compliant	
	Certificate of Conformance:
View	
	Reach 233:
Compliant	

Product Details

- Specialized Plates Designed to Hold and Position Optics
- Filter Holder Plate with Interchangeable Filter Holder

These specialized TECHSPEC® Cage System Filter Holder Plates and Filter Holders are designed to hold and position a range of [optical components](#). Like a standard cage system plate, the anodized aluminum, U-shaped Filter Holder Plate features 6mm rod holes, in addition to being able to accept a Delrin® interchangeable filter holder that easily slides into the filter holder plate.

Quick Video Demonstration

Maximize your application performance with the right products. View a quick video demonstration of TECHSPEC Cage System components: [Filter Holder Plate and Interchangeable Filter Holder](#).