

TECHSPEC® 25mm Max Aperture Motorizable Iris



High Performance Motorizable Iris



Stock **#34-292** 3-4 DAYS

- 1 + **€95,00**

ADD TO CART

Qty 1-4
€95,00

Qty 5+
€84,20

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type:
Unmounted

Minimum Aperture (mm):
1.4

Maximum Aperture (mm): 25.0
Outer Diameter (mm): 37.0
Construction: Brass-Spring Steel
Number of Leaves: 14
Thickness (mm): 5.50
Pitch Diameter (mm): 34.1

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 240: Contains SVHC(s)

