

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

TECHSPEC® 25mm N-SF11 MgF₂ Coated Equilateral Prism



Equilateral Prisms

Stock #47-282 3-4 DAYS



1



€153,00

ADD TO CART

Qty 1-5

€153,00

Qty 6+

€137,70

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Coating:
MgF₂ (400-700nm)

Length of Face (mm):
25.00

Substrate: ☐
[N-SF11](#)

Length (mm): 25.00
Surface Quality: 40-20
Type: Equilateral Prism
Dimensional Tolerance (mm): ±0.1
Angle Tolerance (arcmin): ±2
Image Orientation: Dispersion
Coating Specification: R _{avg} ≤ 1.75% @ 400 - 700nm
Wavelength Range (nm): 400 - 700
Surface Flatness (P-V): λ/4

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View