

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 25mm, Protected Gold Coated, N-BK7 90° Specialty Mirror



Stock #47-238 CONTACT US

1 €180,00

ADD TO CART

Qty 1-5

€180,00

Qty 6+

€144,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Clear Aperture CA (mm):
24.0

Coating:
Protected Gold (700-10000nm)

Substrate: ☐
N-BK7

Surface Quality: 40-20
Type: Right Angle Mirror
Dimensional Tolerance (mm): ±0.1
Angle Tolerance (arcmin): ±2
Bevel: Protective bevel as needed
Clear Aperture (%): 90.00
Length of Hypotenuse (mm): 35.40
Length of Legs (mm): 25.00
Coating Specification: R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm
Wavelength Range (nm): 700 - 10000
Surface Flatness (P-V): λ/8
Coating Type: Metal
Damage Threshold, Reference: ☐ 0.8 J/cm² @ 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant