

## 25mm Square, Blue Dichroic Filter



Additive and Subtractive Dichroic Color Filters

Stock #11-479 3-4 DAYS

⊖ 1 ⊕ **€25,50**

ADD TO CART

Qty 1-24

€25,50

Qty 25+

€22,50

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



**Dimensions (mm):**  
25.0 x 25.0

**Angle of Incidence (°):**  
0

**Cut-Off Wavelength (nm):**  
505.00

Substrate:   
[BOROFLOAT®](#)

Length (mm):  
25.00

Operating Temperature (°C):  
<100

Coating:  
Additive Color

Color:  
Blue

Surface Quality:  
80-50

Thickness (mm):  
2.00 Nominal

Type:  
Dichroic Filter

Width (mm):  
25.00

Dimensional Tolerance (mm):  
±0.25

Clear Aperture (%):  
≥85

Coating Specification:  
T<sub>avg</sub> >85% @ 390 - 485nm, T<sub>avg</sub> <1.0% @ 525 - 750nm  
T<sub>abs</sub> >80% @ 400 - 485nm, T<sub>abs</sub> <1.0% @ 620 - 690nm

Cut-Off Wavelength Tolerance (µm):  
0.012

Regulatory Compliance

RoHS 2015:  
[Compliant](#)

Certificate of Conformance:  
[View](#)

Reach 233:  
[Compliant](#)