

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

TECHSPEC® 25mm VIS-EXT, 50R/50T, Non-Polarizing Cube Beamsplitter



Stock #11-289 3-4 DAYS



1



€283,00

ADD TO CART

Qty 1-5

€283,00

Qty 6+

€222,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Beam Deviation (arcmin):  
≤2

Bevel:  
Protective bevel as needed

Clear Aperture (%):  
>90

|                                                                       |
|-----------------------------------------------------------------------|
| <b>Coating:</b><br>VIS-EXT (400-640nm)                                |
| <b>Coating Specification:</b><br>R <sub>avg</sub> <0.5% @ 400 - 640nm |
| <b>Construction:</b><br>Cube                                          |
| <b>Dimensions (mm):</b><br>25.0 x 25.0 x 25.0 ±0.1                    |
| <b>Reflection/Transmission Ratio (R/T):</b><br>50/50                  |
| <b>Substrate:</b> <a href="#">N-BK7</a>                               |
| <b>Surface Flatness (P-V):</b><br>λ/8                                 |
| <b>Surface Quality:</b><br>40-20                                      |
| <b>Type:</b><br>Non-Polarizing Beamsplitter                           |
| <b>Wavelength Range (nm):</b><br>400 - 640                            |
| <b> Ts-Tp :</b><br><6%                                                |
| <b>Absolute Transmission (%):</b><br>45 ±10                           |

### Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Reach 219:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |