

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 2.5" Dia. X 25" FL Uncoated, Spherical Mirror



Stock #32-081 CLEARANCE 3-4 DAYS

- 1 +

€155,95

ADD TO CART

Qty 1+

€155,95

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Substrate: ☐ BOROFLOAT®

Focal Length Tolerance (%): ±2

Surface Quality: 60-40

Surface Accuracy: λ/8

Diameter (inches): 2.5
Diameter (mm): 63.50 +1.0/-0
Diameter Tolerance (inches): +0.04/-0
Effective Focal Length EFL (inches): 25.0
Effective Focal Length EFL (mm): 635.00
Radius of Curvature (mm): 1,270.00
Aperture (f/#): f/10
Coating: Uncoated
Coating Type: Uncoated
Back Surface: Ground
Edge Thickness ET (inches): 0.38
Edge Thickness ET (mm): 9.65
Edge Thickness Tolerance (%): +0.0/-10
Type: Spherical Mirror

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View