

2.62", English Rotary Stage



Stock #38-193 3-4 DAYS

- 1 + **€1.072,00**

ADD TO CART

Qty 1+
€1.072,00

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Mounting Threads:
(4) 6-32 on 1.125" dia. B.C., (4) 1/4-20 on 2.00" dia. B.C.

Type:
English

Weight (lbs):
1.8

Stage Size (mm):
66.5 x 66.5

Stage Size (inches):

2.62 x 2.62
Construction: Aluminum top and base; steel tangent arm drive
Center Hole: 0.50" Dia. Thru
Travel (°): ±5 (Fine), 360 (Coarse)
Type of Drive: Tangent Arm
Increments (arcmin): 12
Load Capacity, Normal (lbs): 10
Load Capacity, Vertical (lbs): 4
Type of Movement: Rotary
Guide System: Ball Bearing
Table Diameter (inches): 2.62

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View