

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Molded Diffuse Aspheric Condenser Lenses

Stock #22-680 3-4 DAYS



1



€35,00

ADD TO CART

Qty 1-10

€35,00

Qty 11+

€31,50

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
26.50 ±0.20

Effective Focal Length EFL (mm):
18.00

Numerical Aperture NA:
0.67

Back Focal Length BFL (mm): 10.50
Substrate:  Liba2000+
Focal Length Tolerance (%): ±7
Coating: Uncoated
Centering (arcmin): ≤25
Surface Quality: As Molded
Clear Aperture CA (mm): 21.60
Edge Thickness ET (mm): 2.50
Center Thickness CT (mm): 11.37 ±0.20
f/#: 0.75
Bevel: Protective bevel as needed
Diameter of Asphere (mm): 24
Radius R₂ (mm): Plano
Shape of Back Surface: Plano
Wavelength Range (nm): 350 - 2000
Conjugate Distance: Infinite
Note: Maximum of 5 imperfections allowed with an area of 0.8mm, per ISO 10110-7 specification of 5/5 x0.63. Click here for more information on the ISO 10110 surface quality specification.
Grit: Smooth

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant