

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union



SUBMIT

2.70µm CWL, 25.0mm Diameter, 0.11 FWHM, IR Bandpass Filter



Stock #84-069 3-4 DAYS



1



€433,00

ADD TO CART

Qty 1-9

€433,00

Qty 10+

€390,20

Volume Pricing

[Request Quote](#)

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
25.00 +0.00/-0.20

Angle of Incidence (°):
0

Optical Density OD (Average):
≥3.0

Clear Aperture CA (mm):

21.0
Center Wavelength CWL (nm): 2,700.00 ±30
Full Width-Half Max FWHM (nm): 110.00
Substrate: ☐ Sapphire (Al ₂ O ₃)
Coating: Traditional Coated
Surface Quality: 60-40
Thickness (mm): 1.00 ±0.2
Transmission (%): 80 (minimum)
Type: Bandpass Filter
Typical Applications: Water Vapor Emission
Blocking Wavelength Range (nm): 200 - 30000
Center Wavelength CWL (μm): 2.70 ±0.03
Full Width-Half Max FWHM (μm): 0.11 ±0.03

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant