

[All Products](#) / [Test Targets](#) / [Image Analysis & Stage Micrometers](#) / [White Ivory Glass Reticle Targets](#)

[See all 3 Products in Family](#)

27mm Diameter, White Ivory Glass Index Grid Reticle Target



27mm Diameter, White Ivory Glass Index Grid Reticle Target, #58-772



Stock #58-772 3-4 DAYS

$\ominus$ 1 $\oplus$

€223,00

ADD TO CART

Qty 1-4

€223,00

Qty 5+

€212,80

Volume Pricing

[Request Quote](#)

! Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Coating:

Low Reflection Chromium First Surface

Diameter (mm):

27.00 ± 0.050

Substrate: White Ivory Soda Lime Glass
Line Width (mm): 0.0254 ±0.0025
Optical Density OD (Average): OD > 3.0
Pattern Size (mm): 10
Surface Quality: 40-20
Thickness (inches): 1/8
Thickness (mm): 3.20
Edges: Smoothed for Safe Handling
Accuracy (mm): 0.001
Surface Flatness (P-V): 1λ
Reflection (%): < 5% @550nm

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View
