

27mm Diameter x 13mm FL, Aspheric Condenser Lens



Stock **#43-987** ☐ In Stock

[Other Coating Options](#)

1

€49,00

ADD TO CART

Qty 1-10

€49,00

Qty 11+

€43,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
27.00 +0.1/-0.2

Effective Focal Length EFL (mm):
13.00

Numerical Aperture NA:
0.88

Back Focal Length BFL (mm): 6.90
Substrate: B270
Focal Length Tolerance (%): ±7
Coating: Uncoated
Centering (arcmin): ≤25
Surface Quality: 80-50 (typical)
Clear Aperture CA (mm): 21
Edge Thickness ET (mm): 2.0
Center Thickness CT (mm): 9.25 ±0.25
f/#: 0.6
Bevel: Protective bevel as needed
Diameter of Asphere (mm): 23.0
Radius R₂ (mm): Plano
Shape of Back Surface: Plano
Type: Condenser Lens
Wavelength Range (nm): 350 - 2500
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View