

**TECHSPEC® 28mm Max Aperture Motorizable Iris**



High Performance Motorizable Iris



Stock **#34-293** 3-4 DAYS

⊖ 1 ⊕

€100,00

ADD TO CART

Qty 1-4

€100,00

Qty 5+

€88,20

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type:  
Unmounted

Minimum Aperture (mm):  
1.5

|                                            |
|--------------------------------------------|
| <b>Maximum Aperture (mm):</b><br>28.0      |
| <b>Outer Diameter (mm):</b><br>40.0        |
| <b>Construction:</b><br>Brass-Spring Steel |
| <b>Number of Leaves:</b><br>16             |
| <b>Thickness (mm):</b><br>5.50             |
| <b>Pitch Diameter (mm):</b><br>36.96       |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Exempt</a>                |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 240:</b><br><a href="#">Contains SVHC(s)</a>      |