

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

2" Commercial Grade wedge Prism



Stock #27-677 CLEARANCE 3-4 DAYS



1



€24,95

ADD TO CART

Qty 1+

€24,95

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Coating:
MgF₂ (400-700nm)

Angle Tolerance (arcmin):
1.00

Coating Specification:
R_{avg} ≤1.75% @400 - 700nm

Diameter (mm):
25.00 ±0.1

Image Orientation:
Beam Deviation

Power (diopters):
3.49

Substrate: ☐
[N-BK7](#)

Surface Accuracy:
1λ

Thickness (mm):
3.00

Type:
Wedge Prism

Wedge Angle:
3° 52'0"

Wedge Angle Deviation (°):
2.00

Regulatory Compliance

RoHS:
[Compliant](#)

Certificate of Conformance:
[View](#)