

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

2° Diffusing Angle 25mm Dia., Fused Silica Holographic Diffuser



Holographic UV Diffusers

Stock #35-693 3-4 DAYS



1



€457,50

ADD TO CART

Qty 1+

€457,50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Angle Tolerance (°):  
±1

Diffusing Angle (°):  
2 (FWHM)

Clear Aperture CA (mm):  
21.6 ±0.1

Diameter (mm):  
25.00 ±0.1

Operating Temperature (°C):

|                                                               |
|---------------------------------------------------------------|
| -40 to +170                                                   |
| <b>Substrate:</b> <a href="#">Fused Silica</a> (Corning 7980) |
| <b>Transmission (%):</b><br>Typical: 90                       |
| <b>Type:</b><br>Holographic Diffuser                          |
| <b>Wavelength Range (nm):</b><br>400 - 700                    |
| <b>Construction:</b><br>Mounted                               |
| <b>Mount Thickness (mm):</b><br>4.7 ±0.1                      |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 233:</b><br><a href="#">Compliant</a>             |