



TECHSPEC® 2mm Aperture, 25mm L High NA, Hexagonal Light Pipe



N-BK7 Light Pipe Homogenizing Rods



Stock **#48-582** ☒ In Stock



1



€127,50

ADD TO CART

Qty 1-5

€127,50

Qty 6+

€102,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Coating:

Uncoated

Substrate:

N-BK7
Length (mm): 25.00
Surface Quality: 60-40
Type: Light Pipe
Entrance and Exit Aperture (mm): 2.00
Parallelism (arcmin): 5.00
Length Tolerance (mm): ±0.3
Aperture Tolerance (mm): ±0.10
Image Orientation: Light Homogenization
Light Source NA: High
Wavelength Range (nm): 350 - 2200
Surface Flatness (P-V): 1λ

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View