

TECHSPEC® 2" Dia, 2" FL Uncoated, Spherical Mirror



Stock **#32-811** ☐ In Stock

- 1 + **€120,00**

ADD TO CART

Qty 1-9
€120,00

Qty 10+
€102,00

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Substrate: ☐
BOROFLOAT®

Focal Length Tolerance (%):
±2

Surface Quality:
60-40

Surface Accuracy: λ/4
Diameter (inches): 2.0
Diameter (mm): 50.80 +0.5/-0
Diameter Tolerance (inches): +0.02/-0
Effective Focal Length EFL (inches): 2.00
Effective Focal Length EFL (mm): 50.80
Radius of Curvature (mm): 101.60
Aperture (f/#): f/1
Coating: Uncoated
Coating Type: Uncoated
Back Surface: Ground
Edge Thickness ET (inches): 0.50
Edge Thickness ET (mm): 12.70
Edge Thickness Tolerance (%): +0.0/-15
Type: Spherical Mirror

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View