

2" x 2" Green Advanced Illumination Side-Fired Backlight

See More by [Advanced Illumination](#)



Stock **#88-502** 3-4 DAYS



1



€572,00

ADD TO CART

Qty 1+

€572,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Color:
Green

Model Number:
BX0202-530-IC

Operating Temperature (°C):
0 to 60

Dimensions (mm):

115.1 L x 115.1 W x 20.1 D
Wavelength (nm): 530.00
LED Lifetime (hours): 50,000
Power Supply: Power Supply Required and Sold Separately. USA: #66-855 Europe: #66-855 Japan: #66-855 Korea: #33-773 China: #66-855
Number of Channels: 1.00
Active Area (inches): 2 x 2
Type of Illumination: LED Illuminator
Manufacturer: Advanced Illumination
Geometry: Backlight
Illumination Mode: Constant

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Contains SVHC(s)