

2X EO M Plan Apo Long Working Distance Infinity Corrected



50XEO MPlan Apo Long Working Distance Infinity Corrected, #59-879

Stock **#59-875** 3-4 DAYS



1



€948,00

ADD TO CART

Qty 1+

€948,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Field of View (mm):
2

Horizontal Field of View, 1/2" Sensor:
3.20mm

Horizontal Field of View, 2/3" Sensor:
4.40mm

Horizontal Field of View, 1" Sensor:
6.4mm

Focal Length FL (mm):

100.00
Length (mm): 61.00
Length excluding Threads (mm): 61.00
Magnification: 2X
Maximum Diameter (mm): 34
Numerical Aperture NA: 0.055
Mounting Threads: M26 x36 TPI
Compatible Tube Lens Focal Length (mm): Focal Length: 200mm
Type: Microscope Objective
Resolving Power (µm): 5.0
Depth of Field (µm): 91.00
Field of View, 24 Diameter Field Eyepiece (mm): 12.00
Operating Temperature (°C): +10 to +40
Operating Humidity: <85% with no condensation
Working Distance (mm): 34.0
Weight (g): 270
Wavelength Range (nm): 390 - 780
Style: Infinity Corrected
Field Number (mm): 24
Parfocal Length (mm): 95
Immersion Liquid: N/A

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View