

3" Diameter Rotary Plate



Stock **#56-664** 20+ In Stock

-

1

+

€103^{,00}

ADD TO CART

Volume Pricing	
Qty 1-9	€103,00 each
Qty 10+	€91,50 each
Need More?	Request Quote

 Prices shown are exclusive of VAT/local taxes

Product Downloads

General

English	Type:
Rotation	Function:

Physical & Mechanical Properties

12.70	Thickness (mm):
-------	-----------------

Construction: Black Anodized Aluminum and Stainless Steel	
Outer Diameter (mm): 76.2	
Threading & Mounting	
Mounting Threads: (8) ¼-20 Female, (1) ⅜-16 Male	
Regulatory Compliance	
RoHS 2015: Compliant	
Reach 224: Compliant	
Certificate of Conformance: View	

Product Details

- Increase the Versatility of Existing Mounting Equipment
 - Ideal for Direct Mounting to Standard Breadboards
 - Aluminum Plate with ¼-20 Counterbored Holes
- This rotary base plate features slots on a 2" diameter bolt circle which allow adjustments to 70°. Also features a center pin for 360° rotation.

Technical Information

