

# Coherent® StingRay™ Projection Head 1254118 | 514nm, 30° Fan

See More by [Coherent®](#)



30° Line, 514nm Stingray Projection Head, #89-574

Stock **#89-574** **1 In Stock**

⊖ 1 ⊕ €348<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	€348,00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

## Product Downloads



## General

1 Line **Type:**  
**Compatible Laser Models:**  
[86-848, 87-522](#)

Coherent® **Manufacturer:**

## Optical Properties

514.00 **Wavelength (nm):**

Green **Color:**

30.00 **Fan Angle (°):**

## Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

## Product Details

- External Focus with up to 100mW Output Power
- Auto Scaling Input Power 5 - 24VDC with Reverse Polarity Protection
- Built-In Microcontroller for Fault Monitor
- [Coherent® StingRay™ Developer's Kit](#) also available

Coherent® StingRay™ and BioRay™ Laser Diode Modules are ideal for a variety of alignment, machine vision, and biomedical applications. They are available in a wide range of output powers, wavelengths, and fan angles. High precision optical components and sophisticated drive electronics provide power and control to your application, reducing signal-to-noise ratios and increasing measurement speed. Coherent® StingRay™ and BioRay™ Laser Diode Modules are designed with a flat top power distribution across the beam profile for consistency in line projection widths.

**Note:** For CDRH certified systems (Class IIIb), [#86-878](#) Laser Controller and additional external voltage source (0.5-5V) with BNC connector is required.