

Coherent® StingRay™ Projection Head 1277549 | 785nm, 30° Fan

See More by [Coherent®](#)



Stock #89-589 1 In Stock

-

1

+

€351^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	€351,00 each
Need More?	Request Quote

ⓘ

 Prices shown are exclusive of VAT/local taxes

Product Downloads



General

Type:	
1 Line, Extended Focus	
Compatible Laser Models:	
87-527 , 87-528	
Manufacturer:	
Coherent®	

Optical Properties	
785.00	Wavelength (nm):
Infrared	Color:
30.00	Fan Angle (°):
Regulatory Compliance	
Exempt	RoHS 2015:
Contains SVHC(s)	Reach 224:
View	Certificate of Conformance:

Product Details

- External Focus with up to 100mW Output Power
- Auto Scaling Input Power 5 - 24VDC with Reverse Polarity Protection
- Built-In Microcontroller for Fault Monitor
- [Coherent® StingRay™ Developer's Kit](#) also available

Coherent® StingRay™ and BioRay™ Laser Diode Modules are ideal for a variety of alignment, machine vision, and biomedical applications. They are available in a wide range of output powers, wavelengths, and fan angles. High precision optical components and sophisticated drive electronics provide power and control to your application, reducing signal-to-noise ratios and increasing measurement speed. Coherent® StingRay™ and BioRay™ Laser Diode Modules are designed with a flat top power distribution across the beam profile for consistency in line projection widths.

Note: For CDRH certified systems (Class IIIb), [#86-878](#) Laser Controller and additional external voltage source (0.5–5V) with BNC connector is required.