

3.0" Angle Mirror Mount



3.0" Angle Mirror Mount

Stock **#36-481** 20+ In Stock

-

1

+

€250⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-4	€250,00 each
Qty 5-9	€221,20 each
Qty 10-25	€204,10 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
Type:	Adjustable - Tip-Tilt
Type of Optics:	Square or Rectangular
Number of Adjustment Screws:	2

Physical & Mechanical Properties

1.0	Weight (lbs):
	Construction: Black Anodized Aluminum, Stainless Steel
12	Fine Tilt Angle (°):
0.015	Resolution (inches):
12	Fine Tip Angle (°):
0.015	Adjustment Screw Pitch (inches):

Threading & Mounting

12.7 - 76.2	Size of Compatible Optics (mm):
3.0 Sq.	Mounting Plate Size (inches):
(21) ¼-20 on 0.5" Center	Mounting Plate Screw Holes:

Regulatory Compliance

Compliant	RoHS 2015:
Compliant	Reach 224:
View	Certificate of Conformance:

Product Details

- 3.0", 4.5", or 6.0" Square Mounting Surface
- Fine Adjustment Screws (64-Pitch) Allow for Tilting
- Mounting Plate with ¼-20 Threaded Holes

Medium and Large Angle Mirror Mounts are available with a range of mounting plate sizes for mounting optical mirrors. These optical mirror mounts feature 64-pitch fine adjustment screws, allowing for precision tilting in two directions. Both square and rectangular optics can be mounted into these black anodized aluminum and stainless-steel mounts. Medium and Large Angle Mirror Mounts have two ¼-20 through holes on their angle bases for easy mounting to optical tables or breadboards. These mounts are available in 3", 4.5", and 6" sizes.

Technical Information

