

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #21-568 3-4 DAYS



1



€119,00

ADD TO CART

Qty 1-9

€119,00

Qty 10+

€113,40

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Optical Density OD (Average):
3.0

Clear Aperture CA (mm):
32.50

Filter Thread:
M37 x0.50

Substrate: ☐

ND Filter Glass
Surface Quality: 40-20
Transmission (%): 0.10
Type: Mounted Imaging Filter
Blocking Wavelength Range (nm): 425 - 675
Mount Thickness (mm): 5.2
Mount Thickness Including Threads (mm): 7.0

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View
