

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 30 X 30mm Protected Gold, λ/20 Mirror



Stock #34-379 3-4 DAYS

1 €250,00

ADD TO CART

Qty 1-5

€250,00

Qty 6+

€199,50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Surface Flatness (P-V):
λ/20 (flatness pre-coating)

Substrate:
[Fused Silica](#) (Corning 7980)

Back Surface:
Commercial Polish

Surface Quality: 20-10
Dimensions (mm): 30.0 x 30.0 +0.00/-0.20
Coating Specification: R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm
Coating: Protected Gold (700-10000nm)
Coating Type: Metal
Clear Aperture (%): 90.00
Edges: Ground, protective bevel as needed
Parallelism (arcsec): 30.00
Thickness (mm): 5.00
Type: Flat Mirror
Wavelength Range (nm): 700 - 10000
Length (mm): 30.00
Width (mm): 30.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant