

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

300 Grooves/mm, 25mm Sq, UV Transmission Grating Beamsplitter



Stock #85-291 ☐ In Stock



1



€232,50

ADD TO CART

Qty 1-9

€232,50

Qty 10+

€209,50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Groove Density (grooves/mm):  
300

Wavelength Range (nm):  
250 - 500

Blaze Angle (°):  
8.6

|                                                               |
|---------------------------------------------------------------|
| <b>Dimensions (mm):</b><br>25.00 x25.00                       |
| <b>Construction:</b><br>Blazed Grating                        |
| <b>Length (mm):</b><br>25.00                                  |
| <b>Substrate:</b> <a href="#">Fused Silica</a> (Corning 7980) |
| <b>Thickness (mm):</b><br>2.00 ±0.5                           |
| <b>Type:</b><br>Transmission Diffraction Grating              |
| <b>Width (mm):</b><br>25.00                                   |
| <b>Alignment of Grooves to Edge (°):</b><br>±0.5              |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Reach 219:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |