

**TECHSPEC® 300 x 300mm Linear Plastic Polarizer (XP42-200)**



Stock **#86-199** 3-4 DAYS

- 1 + **€220,00**

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-5                       |
| €220,00                       |
| Qty 6+                        |
| €175,00                       |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Extinction Ratio:  
9000:1

Substrate: ☐  
[XP42-200 on PMMA](#)

Length (mm):  
300.00

Operating Temperature (°C):

|                                                                           |
|---------------------------------------------------------------------------|
| -40 to +80                                                                |
| <b>Dimensions (mm):</b><br>300.0 x 300.0 +0.0/-2.0                        |
| <b>Thickness (mm):</b><br>2.22 ±0.25                                      |
| <b>Transmission (%):</b><br>Single: 42<br>Parallel: 36<br>Crossed: <0.004 |
| <b>Type:</b><br>Linear Polarizer                                          |
| <b>Construction:</b><br>Polarizing Film on PMMA                           |
| <b>Wavelength Range (nm):</b><br>400 - 700                                |
| <b>Polarization Efficiency (%):</b><br>>99.98                             |
| <b>Width (mm):</b><br>300.00                                              |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |