

300mm Dia x 42mm FL Alum. Coated, Parabolic Reflector



Stock #90-966 3-4 DAYS

- 1 + **€1.396,00**

ADD TO CART

Qty 1-10
€1.396,00

Qty 11+
€1.230,50

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Substrate: [BOROFLOAT®](#)

Diameter (mm):
300.00 +0.0/-0.5

Focal Length FL (mm):
42.00

Aperture (f#):

0.140
Coating: Protected Aluminum (400-700nm)
Coating Specification: R _{avg} >85% @ 400 - 700nm
Coating Type: Metal
Center Hole Diameter (mm): No Center Hole
Height (mm): 130.0
Type: Parabolic Mirror
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View