

3.00" x 3.00", 6.0" FL, Cylinder Fresnel Lens



Cylinder Fresnel Lenses

Stock **#43-033** [CONTACT US](#)

-

1

+

€46,00

ADD TO CART

Qty 1-10

€46,00

Qty 11+

€40,50

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Effective Focal Length EFL (mm):
152.40

Substrate: ☐
Acrylic

Coating:
Uncoated

Type: Fresnel Lens
Wavelength Range (nm): 400 - 1100
Center Thickness CT (inches): 0.06
Dimensional Tolerance (inches): ±0.05
Dimensions (inches): 3.0 x 3.0
Dimensions (mm): 76.2 x 76.2
Effective Focal Length EFL (inches): 6.00
Effective Size (inches): 3.0 x 3.0
Groove Density (grooves/inch): 65.00
Index of Refraction n_d: 1.49
Operating Temperature (°C): 80 (Maximum)
Transmission (%): 85 (Typical)
Thickness Tolerance (inches): ±0.020

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View