

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #69-921-000 3-4 DAYS



1



€7.345,00

ADD TO CART

Qty 1-2

€7.345,00

Qty 3+

€6.978,00

Volume Pricing

Uncoated
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 0.52 (+5 to +35°C) 0.57 (0 to +200°C) 0.48 (-100 to +200°C)
Diameter (mm): 304.80 +0.00/-1.00
Thickness (mm): 38.10 ±2.5
Diameter (inches): 12.00 +0.00/-0.04
Thickness (inches): 1.50 ±0.10
Clear Aperture CA (mm): 274.30
Color: Clear
Construction: Single Surface
Density (g/cm³): 2.20
Index of Refraction n_d: 1.458
Knoop Hardness (kg/mm²): 522
Parallelism (arcmin): ≤3
Poisson's Ratio: 0.16
Substrate: Fused Silica
Surface Quality: 60-40
Type: Interferometry Window
Wavelength Range (nm): 200 - 2200
Young's Modulus (GPa): 73
Bevel: Protective as needed

Regulatory Compliance

RoHS 2015: Compliant
Reach 211: Compliant
Certificate of Conformance: View