

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

TECHSPEC® 30mm, 40mm Radius, Metric Goniometer



TECHSPEC® Goniometers



Stock #66-523 3-4 DAYS



1



€365,00

ADD TO CART

Qty 1-2

€365,00

Qty 3+

€318,30

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type of Movement:
Goniometer

Type of Drive:
Lead Screw

Type: Metric
Stage Size (mm): 30 x 30
Travel (°): ±15
Construction: Brass Stage
Leadscrew Pitch (mm): 0.5
Load Capacity (kg): 2
Mounting Threads: (1) M6 x 1, (8) M2 x 0.4
Radius R (mm): 40
Resolution (arcmin): 5
Stage Size (inches): 1.18 x 1.18
Weight (kg): 0.15

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant