

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 30mm, 60mm Radius, Metric Goniometer



TECHSPEC® Goniometers



Stock #66-524 3-4 DAYS

- 1 +

€417,00

ADD TO CART

Qty 1-2

€417,00

Qty 3+

€363,60

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type of Movement:  
Goniometer

Type of Drive:  
Lead Screw

|                                                      |
|------------------------------------------------------|
| <b>Type:</b><br>Metric                               |
| <b>Stage Size (mm):</b><br>30 x 30                   |
| <b>Travel (°):</b><br>±10                            |
| <b>Construction:</b><br>Brass Stage                  |
| <b>Leadscrew Pitch (mm):</b><br>0.5                  |
| <b>Load Capacity (kg):</b><br>2                      |
| <b>Mounting Threads:</b><br>(1) M6 x 1, (8) M2 x 0.4 |
| <b>Radius R (mm):</b><br>60                          |
| <b>Resolution (arcmin):</b><br>5                     |
| <b>Stage Size (inches):</b><br>1.18 x 1.18           |
| <b>Weight (kg):</b><br>0.15                          |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 233:</b><br><a href="#">Compliant</a>             |