

TECHSPEC[®] 30mm Barrel for 25.0mm Dia. Achromats



TECHSPEC Mounted Achromatic Lens Pairs

Stock **#54-514** 20+ In Stock

-

1

+

€63^{.50}

ADD TO CART

Volume Pricing	
Qty 1-5	€63,50 each
Qty 6-25	€51,00 each
Qty 26-49	€50,00 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

Physical & Mechanical Properties	
30 +0.0/-0.10	Housing Diameter (mm):
34 ±0.2	Housing Length (mm):
8	Lens Edge Spacing at Mount (mm):

Product Details

- 15mm and 30mm Diameter Options
- AR Coated Lenses
- Mounted Achromatic Pairs Kits Available

TECHSPEC® Mounted Achromatic Lens Pairs combine popular TECHSPEC® Achromats into common configurations used for relay and projection applications. Packaged in slim-line aluminum housing, each pair is ready for integration into a host of OEM applications, eliminating the need to handle loose optics. 15.0mm pairs can be coupled into C-mount components using [Helicoid Barrel Accessory](#). TECHSPEC Mounted Achromatic Lens Pairs have also been oriented for optimum system performance. All lenses, 15.0mm and 30.0mm, are AR coated. Lower f/# pairs may not be ideal for imaging applications depending on the performance requirements. Cylinder lenses can be incorporated into empty barrels in order to generate lines or sheets of light.

Technical Information

