

TECHSPEC® 30mm, Center Drive, Standard Top, 0.25" Travel, English Micrometer



Stock #83-503 **20+ In Stock**

⊖ 1 ⊕ €438⁰⁰

ADD TO CART

Volume Pricing

Qty 1-2	€438,00 each
Qty 3+	€382,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

English **Type:**

Physical & Mechanical Properties


Linear (X) **Type of Movement:**

Crossed Roller Bearing **Guide System:**

30mm Standard-Top Stages - Center Drive




30mm Standard-Top Stages - Side Drive




40mm Standard-Top Stages - Center Drive




40mm Standard-Top Stages - Side Drive



70mm Standard-Top Stages - Center Drive



70mm Standard-Top Stages - Side Drive



125mm Standard-Top Stages - Center Drive



125mm Standard-Top Stages - Side Drive

