

30mm Dia. 750-850nm, NIR Linear Polarizer



Stock #48-893 3-4 DAYS

- 1 + **€370,00**

ADD TO CART

Qty 1-5
€370,00

Qty 6+
€314,00

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Coating:
AR Coating

Diameter (mm):
30.00

Extinction Ratio:
1000:1

Substrate: Polymer Film on B270
Operating Temperature (°C): -25 to +65
Thickness (mm): 2.00
Thickness Tolerance (mm): ±0.2
Transmission (%): 30.00
Transmission Tolerance (%): ±3
Type: Linear Polarizer
Parallelism (arcmin): <4
Dimensional Tolerance (mm): +0.0/-0.2
Construction: Dichroic Polarizing Film on Glass
Wavelength Range (nm): 750 - 850

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View