

TECHSPEC®

30mm Dia. x 75mm FL VIS-EXT, Inked, Double-Convex Lens



Stock **#89-190-INK** [CONTACT US](#)

[Other Coating Options](#)

-

1

+

€68,00

ADD TO CART

Qty 1-9
€68,00
Qty 10+
€61,25
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
30.00 ±0.025

Back Focal Length BFL (mm):
73.35

Effective Focal Length EFL (mm): 75.00
Coating: VIS-EXT (350-700nm)
Coating Specification: R _{avg} <0.5% @ 350 - 700nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Centering (arcmin): <1
Bevel: Protective bevel as needed
Center Thickness CT (mm): 4.96
Center Thickness Tolerance (mm): ±0.10
Edge Thickness ET (mm): 2.00
Radius R₁=R₂ (mm): 76.67
Clear Aperture CA (mm): 29.00
f/#: 2.5
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Numerical Aperture NA: 0.20
Type: Double-Convex Lens
Wavelength Range (nm): 350 - 700

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View