

TECHSPEC 30mm, Side Drive, Standard Top, 0.5" Travel, Metric Micrometer



Stock #66-393 In Stock

⊖ 1 ⊕ **€362,00**

ADD TO CART

Qty 1-2

€362,00

Qty 3+

€315,70

Volume Pricing

[Request Quote](#)

! Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type of Movement:
Linear (X)

Guide System:
Crossed Roller Bearing

Type of Drive:
Metric Micrometer

Drive Orientation:
Side Drive

Type:
Metric

Stage Size (mm):
30 x 30

Travel (mm):
13

Center Hole:
M6 x 1

Construction:
Aluminium Stage

Leadscrew Pitch (mm):
0.5

Load Capacity (kg):
3

Mounting Threads:
(1) M6 x 1, (6) M2 x 0.4

Stage Size (inches):
1.18 x 1.18

Straight Line Accuracy (µm):
2

Pitch (arcsec):
30

Yaw (arcsec):
25

Regulatory Compliance

RoHS 2015:
[Exempt](#)

Certificate of Conformance:
[View](#)

REACH 241:
[Contains SVHC\(s\)](#)
