

TECHSPEC[®] 30mm SQ Dovetail Stage Base Plate



#17-289: 30mm SQ Dovetail Stage Base Plate



Stock **#17-289** 9 In Stock

-

1

+

€33^{.25}

ADD TO CART

Volume Pricing	
Qty 1-9	€33,25 each
Qty 10+	€30,00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Type:

Universal	
Bottom Adapter	Function:
30	Compatible Stage Size (mm):
Physical & Mechanical Properties	
30.00	Length (mm):
11.40	Thickness (mm):
65.00	Width (mm):
Black Anodized Aluminum	Construction:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 233:

PRODUCT DETAILS

- Compact Overall Size for System Integration
- Brass Construction for High Stiffness and up to 15kg Load Capacity
- Compatible with All TECHSPEC® Stages

TECHSPEC® High Load Capacity Dovetail Stages are a compact, cost-effective solution for linear adjustment within an optical system. These stages feature high stiffness brass construction and a hex driven movement, allowing for a low profile and compact overall size with 5, 10, and 15kg high load capacity options. The absence of tension springs and the included external plate lock ensure resistance to vibration and increase stability. TECHSPEC High Load Capacity Dovetail Stages are ideal for imaging and laser optics systems that require low profile integrated linear adjustments in demanding environments. These stages feature bolt patterns that are compatible with all TECHSPEC and comparable metric and English stages.

TECHNICAL INFORMATION



