

TECHSPEC® 30mm, Uncoated, N-BK7 Right Angle Prism



N-BK7 Right Angle Prisms

Stock **#32-527** 3-4 DAYS

⊖ 1 ⊕ **€95,00**

ADD TO CART

Qty 1-5
€95,00

Qty 6+
€85,50

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Coating:

Uncoated

Substrate: ☐

[N-BK7](#)

Surface Quality:

60-40

Type: Right Angle Prism
Dimensional Tolerance (mm): ±0.1
Angle Tolerance (arcmin): ±2
Bevel: Protective bevel as needed
Length of Hypotenuse (mm): 42.40
Length of Legs (mm): 30.00
Image Orientation: Left-Handed
Ray Deviation (°): 90
Wavelength Range (nm): 350 - 2200
Surface Flatness (P-V): λ/4

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View